





- The patient's position can be adjusted according to different conditions, the head backrest angle can be adjusted with a maximum angle of $>75^{\circ}$ and the leg angle of $>10^{\circ}$.
- The stretcher wheels adopt wear-resistant silent wheel technology with universal positioning brake function. The diameter of the front wheel is $>150\text{mm}$, and the diameter of the rear wheel is $>125\text{mm}$. The stretcher is equipped with self-locking devices to prevent accidental contact and protect the patient's safety and transfer.



DIMENSIONS AND WEIGHT:

		Unfolding size	Folding size
H	Height(mm)	850	250
HC	Height from floor to leading wheel(mm)	630	/
W	Width(mm)	550	550
L	Length(mm)	1950	1950
	Weight(kg)	39	39

RELATED PRODUCT

