





- The patient's position can be adjusted according to different conditions, the head backrest angle can be adjusted with a maximum angle of $>75^\circ$ and the leg angle of $>10^\circ$.
- The stretcher wheels adopt wear-resistant silent wheel technology with universal positioning brake function. The diameter of the front wheel is $>150\text{mm}$, and the diameter of the rear wheel is $>125\text{mm}$. The stretcher is equipped with self-locking devices to prevent accidental contact and protect the patient's safety and transfer.



DIMENSIONS AND WEIGHT:

		S	M	L	XL
H	Height(mm)	310	/	/	925
HC	Height from floor to leading wheel(mm)	575	600	625	650
W	Width(mm)	545	545	545	545
L	Length(mm)	1985	1985	1985	1985
	Weight(kg)	38.5	38.5	38.5	38.5

RELATED PRODUCT

